



Adams part no.	Dimensions	Base	Westinghouse part no.
W75K2	1 3/4" L x 1" W x 3/8"	B	X38-K2
W75K7	1 3/4" L x 1 1/4" W x 1/2"	B	X38-K7
W75K8	1 3/4" L x 1" W x 3/8"	B	X38-K8
W75K12	1 1/2" L x 1" W x 3/8"	B	X38-K12
W75K13	1 3/4" L x 1" W x 3/8"	B	X38-K13
W75K14	1 3/4" L x 1" W x 1/2"	B	X38-K14
W75K15	1 3/4" L x 1 1/4" W x 1/2"	B	X38-K15
W75L1	1 1/2" L x 1" W x 1/2"	S	X38-L1
W75L2	1 1/2" L x 1 1/2" W x 1/2"	S	X38-L2
W75L9	1 3/4" L x 1 1/2" W x 1/2"	S	X38-L9
W75L10	1 1/2" L x 1 1/2" W x 1/2"	S	X38-L10
W75L11	1 1/2" L x 1" W x 1/2"	S	X38-L11
W75Q1	1 1/2" L x 1" W x 3/8"	A	X38-Q1
W75Q2	1 1/2" L x 1" W x 1/2"	A	X38-Q2
W75Q3	1 1/2" L x 1 1/2" W x 1/2"	A	X38-Q3
W75Q9	1 1/2" L x 1 1/2" W x 5/8"	A	X38-Q9
W75Q10	1 1/2" L x 1 1/2" W x 1/2"	A	X38-Q10
W75Q11	1 3/4" L x 1 1/2" W x 5/8"	A	X38-Q11
W75Q12	1 3/4" L x 1" W x 3/4"	A	X38-Q12
W75Q14	1 1/2" L x 1 1/2" W x 5/8"	A	X38-Q14
W75Q16	1 3/4" L x 1 1/2" W x 3/4"	A	X38-Q16
W75Q20	1 3/4" L x 1 1/2" W x 5/8"	A	X38-Q20
W75Q22	1 1/2" L x 1" W x 1/2"	A	X38-Q22
W75Q34	1 1/2" L x 1 1/2" W x 5/8"	A	X38-Q34
W75Q35	1 1/2" L x 1 1/2" W x 1/2"	S	X38-Q35
W75Q36	1 3/4" L x 1 1/2" W x 5/8"	S	X38-Q36
W75Q37	1 3/4" L x 1 1/2" W x 3/4"	A	X38-Q37
W75Q38	1 3/4" L x 1 1/2" W x 1"	A	X38-Q38

Adams part no.	Dimensions	Base	Westinghouse part no.
W75M3	1 1/4" L x 1" W x 3/8"	F	X38-M3
W75M9	1 1/4" L x 1" W x 3/8"	F	X38-M9
W75M10	1 3/4" L x 1 1/2" W x 5/16"	F	X38-M10
W75M11	1 1/2" L x 1 1/2" W x 3/8"	F	X38-M11
W75M12	1 1/2" L x 1 1/2" W x 5/16"	F	X38-M12
W75M15	1 1/4" L x 1" W x 3/8"	F	X38-M15
W75M16	1 1/2" L x 1 1/2" W x 5/16"	F	X38-M16
W75M20	1 3/4" L x 1 1/2" W x 5/16"	F	X38-M20
W75M21	1 1/4" L x 1" W x 3/8"	F	X38-M21
W75M22	1 3/4" L x 1 1/2" W x 5/16"	F	X38-M22
W75M24	1 1/2" L x 1 1/2" W x 5/16"	F	X38-M24
W75M25	1 3/4" L x 1 1/2" W x 1/2"	F	X38-M25
W75N1	3/4" L x 5/16" W x 1/4"	F	X38-N1
W75N2	1" L x 5/16" W x 1/4"	F	X38-N2
W75R1	1 1/4" L x 1" W x 3/8"	F	X38-R1
W75R2	1 1/4" L x 1" W x 3/8"	F	X38-R2
W75R4	1 1/2" L x 1 1/2" W x 3/8"	F	X38-R4
W75R5	1 1/2" L x 1 1/2" W x 1/2"	F	X38-R5
W75R10	1 1/4" L x 1" W x 3/8"	F	X38-R10
W75R11	1 1/2" L x 1 1/2" W x 3/8"	F	X38-R11
W75R12	1 1/2" L x 1 1/2" W x 1/2"	F	X38-R12
W75R13	1 1/2" L x 1 1/2" W x 5/8"	F	X38-R13
W75R14	1 1/4" L x 5/8" W x 3/8"	F	X38-R14
W75R15	1 1/2" L x 1" W x 1/2"	F	X38-R15
W75R16	1 1/2" L x 1 1/2" W x 3/8"	F	X38-R16
W75R18	1 1/4" L x 5/8" W x 3/8"	F	X38-R18
W75R21	1 1/2" L x 1" W x 3/8"	F	X38-R21
W75R38	1 1/4" L x 1" W x 3/8"	F	X38-R38
W75T1	1/4" dia. x 1" L; 1 5/8" L spring, 1/4" dia.	R	X38-T1
W719	1 1/8" L x 5/8" W x 3/8"; 4 1/2" L shunt	F	spec. W2070
W774	1 3/4" L x 1" W x 3/8"	F	spec. 2176

B=Bevelled; F=Flat; R=Radius Edge; S=Separated; A=Attached Split